


Sanitary Tri-Clamp® Sizing Guide



The sketches shown on this guide are actual size. Simply print the guide with scaling set to none on 8.5" x 11" paper and place the Tri-Clamp® flange on the various pictures to identify the actual size designation. Allow for some slight variances from manufacturer to manufacturer.



Fractional (Mini) Tri-Clamp®

| Size | Flange Diameter | Bore Diameter |
|-----------|-----------------|---------------|
| 1/8" Mini | 0.992 | 0.060 |
| 1/4" Mini | 0.992 | 0.187 |
| 3/8" Mini | 0.992 | 0.275 |
| 1/2" Mini | 0.992 | 0.370 |
| 3/4" Mini | 0.992 | 0.620 |

Note: All dimensions are in inches. Allow 5% variance in dimensions from manufacturer to manufacturer.







1" Maxi Tri-Clamp® is most commonly used in sanitary non-metallic (plastic) fittings and piping systems including polypropylene and PVDF. **1" Ladish®** and **1-1/2" Tri-Clamp®** share the same flange diameter and can also share the same sanitary clamp size.

1" and 1-1/2" Tri-Clamp®

| Size | Flange Diameter | Bore Diameter |
|------------|-----------------|---------------|
| 1" Maxi | 1.485 | 0.870 |
| 1" Ladish® | 1.984 | 0.870 |
| 1-1/2" | 1.984 | 1.370 |

Note: All dimensions are in inches. Allow 5% variance in dimensions from manufacturer to manufacturer.

Sanitary Tri-Clamp® Sizing Guide



2" Thru 6" Tri-Clamp®

| Size | Flange Diameter | Bore Diameter |
|--------|-----------------|---------------|
| 2" | 2.516 | 1.906 |
| 2-1/2" | 3.047 | 2.406 |
| 3" | 3.579 | 2.906 |
| 4" | 4.682 | 3.870 |
| 6" | 6.570 | 5.792 |

Note: All dimensions are in inches. Allow 5% variance in dimensions from manufacturer to manufacturer.